



CHROMATOGRAPHY · FLUID HANDLING

Column Accessories

Single-use components and assemblies designed to support chromatography workflows.


BPSSU provides column accessories and custom single-use assemblies configured around your chromatography and downstream purification workflow. From tubing and connection components to supporting fluid paths, assemblies can be designed around your existing column, equipment, and process requirements.

Supporting Your Chromatography Workflow

Simplify fluid handling by consolidating tubing, fittings, connectors, and related components into practical, ready-to-integrate solutions. BPSSU works with your existing equipment and process requirements to determine the appropriate configuration for your application.

Column Connection Assemblies

Pre-configured assemblies help simplify connections between chromatography columns and FPLC systems where different ports, thread types, and tubing requirements may be involved.



Custom Configuration

Assemblies can be designed around your specific column, equipment, and process requirements.

Integrated Fluid Handling

Combine tubing, fittings, connectors, and other required components into a more complete solution.

Process Compatibility

Solutions are configured around existing equipment, helping minimize the need to redesign your process.

Direct BPSSU Support

Work directly with the BPSSU team to determine the appropriate components and configuration for your application.

BPSSU Standard Design

Choose from one of our standard designs configured for the following systems below.

Available configurations support:

Millipore /
Omnifit

Repligen

Cytiva

ÄKTA systems

FEP and PTFE
tubing options

Multiple tubing dimensions for varying flow requirements